

UBE NYLON 1030MB

Technical Product Information: Monofilament properties

UBE NYLON 1030MB is a soft high viscosity Polyamide 6 homopolymer. The grade is suitable for monofilament applications where high flexibility is requested. This material has the following features:

- Good processability
- Good mechanical properties
- Superior flexibility

Basic Properties ⁽¹⁾	Method	Unit	Value
Polymer	-	-	PA6
Melting Point	ISO 11357	°C	213
Relative Viscosity (96% H₂SO₄)	JIS K6810	-	3,77
Density	DIN 53479	g/cm ³	1,13

Mechanical Properties ⁽²⁾ Unit Value

Mechanical properties of monofilament d = 0,3mm								
Draw ratio (G3/G1)			4,5	5,0	5,5	6,0	6,5	7,0
Line	Strength	g/d	5,5 - 6,5	6,5 - 7,5	7,5 - 8,5	8,5 - 9,5		
	Tenacity	kg	3,0 - 4,0	4,0 - 5,0	5,0 - 6,0	5,5 - 6,5		
	Elongation	%	28 - 32	26 - 30	22 - 26	20 - 24		
Tensile modulus		g/d	10 - 14	12 - 16	14 - 18	14 - 18		
Knot	Strength	g/d	3,5 - 4,5	3,0 - 4,0	2,5 - 3,5	2,5 - 3,5		
	Tenacity	kg	2,0 - 3,0	1,5 - 2,5	1,5 - 2,5	1,5 - 2,5		
	Elongation	%	16 - 20	12 - 26	10 - 14	10 - 14		
Mechanical properties of monofilament d = 2,0mm								
Draw ratio (G3/G1)			4,5	5,0	5,5	6,0	6,5	7,0
Line	Strength	g/d	4,0 - 5,0	5,0 - 6,0				
	Tenacity	kg	140 - 160	170 - 190				
	Elongation	%	26 - 30	24 - 28				
Tensile modulus		g/d	10 - 14	12 - 16				
Knot	Strength	g/d	1,5 - 2,5	1,0 - 2,0				
	Tenacity	kg	50 - 70	40 - 60				
	Elongation	%	18 - 22	16 - 20				

(1) Measured on base resin
 (2) All tests carried out on monofilaments produced with a 35mm screw
 Extrusion temperatures between 240-275°C
 Quench bath temperature: 15°C
 Drawing temperature: 1st = 95°C (hot water); 2nd = 180°C; Heat set = 180°C
 Relaxation ratio (G4/G3) = 1; Line speed (G4) = 28 m·min⁻¹
 Sample conditioning and testing conditions: T = 23°C, RH =50%

Processing conditions

	Extruder					Adaptor	Die
	Hopper	Zone 1	Zone 2	Zone 3	Zone 4		
Temperature (°C)	40 - 120	200 - 210	240 - 250	250 - 260	245 - 255	250 - 260	250 - 260

	Quenching bath	1 st drawing	2 nd drawing	Heat setting
Temperature (°C)	8 - 15	90 - 100	170 - 190	170 - 190

Drying conditions

UBE NYLON is supplied dry (moisture content < 0,1%) and packed in high barrier films. However, as polyamide is a hygroscopic material, the user should take a special care of the possible moisture absorption once the bag or liner box has been opened. In case of moisture absorption, the material should be dried with dehumidified air at 80°C for more than 4 hours.

Storage

Well-sealed packages could be stored in cool and dry conditions over long periods of time. Protect the packages from heat and direct sunlight to prevent possible damages.

Health & environmental data

Please refer to the corresponding **UBE NYLON** grade SDS.

IMPORTANT NOTICE:

The contents of here written materials were prepared based on materials, information and data available at the present moment. They may be revised because of new knowledge, information and data without notification. The data described herein are averaged values obtained by specific measurement. They are not guaranteed figures. UBE does not warrant or guarantee the quality or safety of your finished products, including but not limited to implied warranties of merchantability, fitness for a particular purpose and non infringement of third party rights or arising from a course of dealing, usage or trade practice even if UBE's products and data herein or any other information proposed by UBE are used to manufacture the finished products. Determination of suitability, merchantability or fitness for a particular purpose of your finished products shall be on your responsibility. UBE has no liability or legal responsibility for any issues or problems in relation to standards, regulations, laws, intellectual property rights - especially patent rights, etc. derived from any applications of UBE products for your finished products. So it should be fully researched and studied by yourself. UBE highly recommends reading Safety Data Sheet "SDS" before using UBE Products to ensure your safety. "UBE NYLON" and "UBESTA" is registered trademark in Japan and other countries.